

**Angle grinder Deadman, Type: 72210529****Order data**

Order number	077152 72210529
GTIN	4014586851792
Item class	03F

**Description****Version:**

- **FEIN high power motor with enormous traction power for high removal rates.**
- **Automatic restart inhibit after power supply interruption.**
- **Rear handle can be turned to 4 positions.**

**Dead man's switch**, i.e. can be operated only when both hands are on the machine. Without locking On / Off switch.

- **Non-wearing EBS electrical braking system stops the machine in less than 3 seconds.**
- **FEIN quick-release clamping system QuickIN for quick easy and reliable disc changes without using tools.**

**Function:**

IP20: No protection against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and no protection against water.

**Supplied with:**

Supplied with protective hood, additional handle, clamping set.

Manufacturer's designation: WSB20-180

Power consumption: 2000 W

maximum speed: 8,500 min<sup>-1</sup>

maximum disc  $\varnothing$ : 180 mm

maximum cutting depth: 48 mm

Weight: 4.8 kg

**Technical description**

maximum disc $\varnothing$	180 mm
----------------------------	--------

Manufacturer's designation	WSB20-180
maximum speed	8,500 min <sup>-1</sup>
Special features	QuickIN
maximum cutting depth	48 mm
Power consumption	2000 W
maximum vibration to EN	6 m/s <sup>2</sup>
Weight	4.8 kg
Dead man's circuit	yes
Power supply	Mains operated
Type of product	Angle grinder