

**Garant**
**Combination face mill adapter, HSK-F 63 short, Spigot  $\varnothing$  d1: 32mm**

**Order data**

Order number	306121 32
GTIN	4045197587787
Item class	31A

**Description**
**Version:**

With RFID/Balluffchip bore. HSK mating faces machined.

**Application:**

For clamping shell end mills and milling cutter heads with longitudinal or transverse groove.

**Supplied with:**

Including drive key, face mill drive ring, and milling cutter lock screw No. 309860.

**Optional extras:**

Toggle spanner No. 309840, locking screw for internal coolant supply No. 309861.

**Note:**

Without a thread for the coolant pipe.

Internal cooling available only with suitable tightening screw No. 309861.

**Technical description**

Overhang dimension A	65 mm
Milling mandrel length $L_4$	38 mm
Spare drive ring No. 309870	32
Suitable toggle spanner No. 309840	32
Milling mandrel length $L_3$ with drive ring	24 mm
Spigot $\varnothing$ d <sub>1</sub>	32 mm

External Ø D	58 mm
Spare milling cutter lock screw No. 309860 / 309861	32
Clamping Ø D <sub>1</sub>	32 mm
Adapter	HSK-F 63 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Shape	F
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling cutter spigot

---

## Accessories

Milling cutter lock screw for mandrel Ø 32 mm	309860 32
Face mill drive ring for mandrel Ø 32 mm	309870 32
Toggle spanner for mandrel Ø 32 mm	309840 32