



ET collet for thread tapping, with axial compensation, ET 40, Nominal clamping Ø d: 10 mm



Order data

Order number	309434 10
GTIN	2050001704184
Item class	34F

Description

Version:

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20 µm.

Application:

For tapping on milling and turning centres.

Suitable for :

All standard ER collet chucks.

Note:

Clamps only the nominal Ø. **Not compatible with the CENTRO P precision ER collet chuck.**

Norm: Manufacturer's standard

Type: 4717 E

External Ø D: 41 mm

Overall length L: 54 mm

Axial range: 13 mm

Technical description

Nominal clamping Ø d	10 mm
Adapter	ET 40
Norm	Manufacturer's standard
Type	4717 E

External Ø D	41 mm
Overall length L	54 mm
Axial range	13 mm