

FAHRION®
PRAZISION

ET collet for thread tapping, with axial compensation, ET 20, Nominal clamping \varnothing d: 7 mm



Order data

Order number	309428 7
GTIN	2050001703996
Item class	34F

Description

Version:

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20 μ m.

Application:

For tapping on milling and turning centres.

Suitable for :

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Norm: Manufacturer's standard

Type: 4284 E

External \varnothing D: 21 mm

Overall length L: 31 mm

Axial range: 7 mm

Technical description

Nominal clamping \varnothing d	7 mm
Adapter	ET 20
Norm	Manufacturer's standard
Type	4284 E

External Ø D	21 mm
Overall length L	31 mm
Axial range	7 mm