



Angle grinder Deadman, Type: 72210629



Order data

Order number	077152 72210629
GTIN	4014586851815
Item class	03F

Description

Version:

- **FEIN high power motor with enormous traction power for high removal rates.**
- **Automatic restart inhibit after power supply interruption.**
- **Rear handle can be turned to 4 positions.**

Dead man's switch, i.e. can be operated only when both hands are on the machine. Without locking On / Off switch.

- **Non-wearing EBS electrical braking system stops the machine in less than 3 seconds.**
- **FEIN quick-release clamping system QuickIN for quick easy and reliable disc changes without using tools.**

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Supplied with protective hood, additional handle, clamping set.

Manufacturer's designation: WSB20-230

Power consumption: 2000 W

maximum speed: 6,600 min⁻¹

maximum disc \varnothing : 230 mm

maximum cutting depth: 66 mm

Weight: 4.8 kg

Technical description

Special features	QuickIN
------------------	---------

Power consumption	2000 W
Manufacturer's designation	WSB20-230
maximum speed	6,600 min ⁻¹
maximum disc Ø	230 mm
Weight	4.8 kg
maximum cutting depth	66 mm
Dead man's circuit	yes
maximum vibration to EN	6 m/s ²
Power supply	Mains operated
Type of product	Angle grinder