

**FAHRION®**  
FAHRENDEN PRESSION

## ET collet for thread tapping, with axial compensation, ET 16, Nominal clamping $\varnothing$ d: 2,8mm



### Order data

Order number	309425 2,8
GTIN	2050001703927
Item class	34F

### Description

**Version:**

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20  $\mu$ m.

**Application:**

For tapping on milling and turning centres.

**Suitable for:**

All standard ER collet chucks.

**Note:**

Clamps only the nominal  $\varnothing$ . **Not compatible with the CENTRO P precision ER collet chuck.**

### Technical description

Nominal clamping $\varnothing$ d	2.8 mm
Adapter	ET 16
Standard	Manufacturer's standard
Type	4033 E
External $\varnothing$ D	17 mm
Overall length L	27 mm
Axial range	7 mm

Type of product

Collet