

**FAHRION®**  
FAHRENDEN PRESSION**ET collet for thread tapping, with axial compensation, ET 25, Nominal clamping  $\varnothing$  d: 3,5mm****Order data**

Order number	309430 3,5
GTIN	2050001704009
Item class	34F

**Description****Version:**

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20  $\mu$ m.

**Application:**

For tapping on milling and turning centres.

**Suitable for:**

All standard ER collet chucks.

**Note:**

Clamps only the nominal  $\varnothing$ . **Not compatible with the CENTRO P precision ER collet chuck.**

**Technical description**

Nominal clamping $\varnothing$ d	3.5 mm
Adapter	ET 25
Standard	Manufacturer's standard
Type	4285 E
External $\varnothing$ D	26 mm
Overall length L	34 mm
Axial range	8 mm

Type of product

Collet