

**FAHRION®**  
FAHRENDEN PRESSION

## ET collet for thread tapping, with axial compensation, ET 25, Nominal clamping $\varnothing$ d: 6mm



### Order data

Order number	309430 6
GTIN	2050001704023
Item class	34F

### Description

**Version:**

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20  $\mu$ m.

**Application:**

For tapping on milling and turning centres.

**Suitable for:**

All standard ER collet chucks.

**Note:**

Clamps only the nominal  $\varnothing$ . **Not compatible with the CENTRO P precision ER collet chuck.**

### Technical description

Nominal clamping $\varnothing$ d	6 mm
Adapter	ET 25
Standard	Manufacturer's standard
Type	4285 E
External $\varnothing$ D	26 mm
Overall length L	34 mm
Axial range	8 mm

Type of product

Collet