

FAHRION®
FAHRENDEN PRESSION

ET collet for thread tapping, with axial compensation, ET 16, Nominal clamping \varnothing d: 4,5mm



Order data

Order number	309425 4,5
GTIN	2050001703941
Item class	34F

Description

Version:

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20 μ m.

Application:

For tapping on milling and turning centres.

Suitable for:

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Technical description

Nominal clamping \varnothing d	4.5 mm
Adapter	ET 16
Standard	Manufacturer's standard
Type	4033 E
External \varnothing D	17 mm
Overall length L	27 mm
Axial range	7 mm

Type of product

Collet