



Clamping head smooth, SK 65, Clamping \varnothing (0.5 mm increments): 5,5mm



Order data

Order number	329930 5,5
GTIN	2050001075178
Item class	33H

Description

Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	5.5 mm
Hardness	60 HR
Profile	round
Clamping face	smooth
Length L	58 mm

Adapter	SK 65
Type of product	Clamping head