

FAHRION®
FAHRENDEN PRESSION

ET collet for thread tapping, with axial compensation, ET 25, Nominal clamping \varnothing d: 9mm



Order data

| | |
|--------------|---------------|
| Order number | 309430 9 |
| GTIN | 2050001704054 |
| Item class | 34F |

Description

Version:

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20 μ m.

Application:

For tapping on milling and turning centres.

Suitable for:

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Technical description

| | |
|----------------------------------|-------------------------|
| Nominal clamping \varnothing d | 9 mm |
| Adapter | ET 25 |
| Standard | Manufacturer's standard |
| Type | 4285 E |
| External \varnothing D | 26 mm |
| Overall length L | 34 mm |
| Axial range | 8 mm |

Type of product

Collet