

**FAHRION®**  
PRAZISION

## ET collet for thread tapping, with axial compensation, ET 40, Nominal clamping $\varnothing$ d: 6 mm



### Order data

Order number	309434 6
GTIN	2050001704153
Item class	34F

### Description

**Version:**

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20  $\mu$ m.

**Application:**

For tapping on milling and turning centres.

**Suitable for :**

All standard ER collet chucks.

**Note:**

Clamps only the nominal  $\varnothing$ . **Not compatible with the CENTRO P precision ER collet chuck.**

Norm: Manufacturer's standard

Type: 4717 E

External  $\varnothing$  D: 41 mm

Overall length L: 54 mm

Axial range: 13 mm

### Technical description

Nominal clamping $\varnothing$ d	6 mm
Adapter	ET 40
Norm	Manufacturer's standard
Type	4717 E

External Ø D	41 mm
Overall length L	54 mm
Axial range	13 mm