

FAHRION®
FAHRENDEN PRESSION

ET collet for thread tapping, with axial compensation, ET 25, Nominal clamping \varnothing d: 10mm



Order data

Order number	309430 10
GTIN	2050001704061
Item class	34F

Description

Version:

Collet for thread tapping, similar to DIN 6499 / ISO 15488, Form CET-GB, concentricity 20 μ m.

Application:

For tapping on milling and turning centres.

Suitable for:

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Technical description

Nominal clamping \varnothing d	10 mm
Adapter	ET 25
Standard	Manufacturer's standard
Type	4285 E
External \varnothing D	26 mm
Overall length L	34 mm
Axial range	8 mm

Type of product

Collet