



## Clamping head smooth, SK 65, Clamping $\varnothing$ (0.5 mm increments): 7mm



### Order data

Order number	329930 7
GTIN	2050001072504
Item class	33H

### Description

#### Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

#### Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

Clamping $\varnothing$	7 mm
Profile	round
Hardness	60 HR
Clamping face	smooth
Length L	58 mm

Adapter	SK 65
Type of product	Clamping head