

**Clamping head soft, SK 52, Initial bore  $\varnothing$ : 8mm****Order data**

Order number	329926 8
GTIN	2050001922625
Item class	33H

**Description****Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

**Application:**

Versatile application range, machining centres, measuring machines or pallet clamping.

**Note:**

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

**Technical description**

Initial bore $\varnothing$	8 mm
Hardness	60 HR
Length L	46 mm
Adapter	SK 52
Type of product	Clamping head

