



Top jaws set, 3 pieces, for chuck type: 315



Order data

Order number	313450 315
GTIN	4019208193472
Item class	33R

Description

Version:

Precision milled slots and serrations, **burnished**.

Bevelled for small clamping \emptyset .

Material:

Quality product made of 16MnCr5.

Suitable for:

Heavy-duty chucks from Schunk, Röhmm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

Slot width D	21 mm
for thread DIN 912	M16
Bore spacing b	28 mm
Hole centre spacing a	30 mm
for chuck type	315 mm
Length L	140 mm

Width B	50 mm
Height H	50 mm
Type of product	Heavy-duty lathe chuck jaws