



Top jaws set, 3 pieces, for chuck type: 170



Order data

Order number	313700 170
GTIN	4019208193663
Item class	33R

Description

Version:

Precision milled slots and serration, **burnished**.

Material:

Quality product made of 16MnCr5.

Suitable for:

Heavy-duty chucks from Schunk, Röhmm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

for thread DIN 912	M10
Hole centre spacing a	15 mm
Length L	72 mm
for chuck type	170 mm
Height H	40 mm
Width B	32 mm
Slot width D	12 mm

Bore spacing b	20 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws