



Clamping head soft, SK 52, Initial bore \varnothing : 30mm



Order data

Order number	329926 30
GTIN	2050001922649
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Initial bore \varnothing	30 mm
Hardness	60 HR
Length L	46 mm
Adapter	SK 52
Type of product	Clamping head

