



Top jaws set, 3 pieces, for chuck type: 250



Order data

Order number	313460 250
GTIN	4019208193502
Item class	32R

Description

Version:

Precision milled slots and serrations, **not burnished**.

Bevelled for small clamping \emptyset .

Material:

Quality product made of 16MnCr5.

Suitable for :

Heavy-duty chucks from Schunk, Röhmm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Length L: 120 mm

Width B: 50 mm

Height H: 50 mm

Hole centre spacing a: 20 mm

Bore spacing b: 28 mm

Slot width D: 21 mm

Technical description

Width B	50 mm
Length L	120 mm
for thread DIN 912	M16

Bore spacing b	28 mm
Slot width D	21 mm
Hole centre spacing a	20 mm
Height H	50 mm
for chuck type	250 mm
Type of product	Heavy-duty lathe chuck jaws