




Top jaws set, 3 pieces, for chuck type: 315/21



Order data

| | |
|--------------|---------------|
| Order number | 313710 315/21 |
| GTIN | 4045197152275 |
| Item class | 32R |

Description

Version:

Precision milled slots and serrations.

Material:

Quality product made of 16MnCr5.

Suitable for :

Heavy-duty chucks from Schunk, Röhmm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

suitable for colour code: Schunk heavy-duty chucks and jaws

Length L: 130 mm

Width B: 50 mm

Height H: 58 mm

Hole centre spacing a: 39 mm

Bore spacing b: 30 mm

Slot width D: 21 mm

Technical description

| | |
|----------|--------|
| Height H | 58 mm |
| Length L | 130 mm |

| | |
|--------------------------|-----------------------------------|
| Slot width D | 21 mm |
| Bore spacing b | 30 mm |
| Hole centre spacing a | 39 mm |
| Width B | 50 mm |
| for thread DIN 912 | M16 |
| for chuck type | 315 mm |
| suitable for colour code | Schunk heavy-duty chucks and jaws |
| Type of product | Heavy-duty lathe chuck jaws |