



Top jaws set, 3 pieces, for chuck type: 250



Order data

Order number	313400 250
GTIN	4019208193397
Item class	33R

Description

Version:

Precision milled slots and serrations, **burnished**.

Material:

Quality product made of 16MnCr5.

Suitable for:

Heavy-duty chucks from Schunk, RöhM and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

Width B	45 mm
Length L	95 mm
also suitable for chuck type	315 mm
for thread DIN 912	M16
for chuck type	250 mm
Hole centre spacing a	15 mm

Slot width D	21 mm
Bore spacing b	25 mm
Height H	54 mm
Type of product	Heavy-duty lathe chuck jaws