

**T-nut annealed, Slot width D: 17mm****Order data**

Order number	313520 17
GTIN	4019208193632
Item class	33R

Description**Version:**

Precision ground, quenched, and tempered.

Suitable for:

All **popular heavy-duty chucks manufactured by** Schunk, Forkardt, Röhmm, and SMW (with sharp serrations).

Suitable for:

Röhmm: KFD 160-200

Supplied with:

Socket head screws DIN 912 - 12.9!

Note:

Other T-nuts available ex works.

Technical description

Height H	21.7 mm
maximum tightening torque	70 Nm
Slot width D	17 mm

Thread G	M12
Step height h	9.5 mm
Type of product	Tee-nut