

Garant
MT reducing adapter for locking threads, HSK-A 63, MT internal: 4

Order data

Order number	306750 4
GTIN	4045197505132
Item class	31A

Description
Version:

- Precision ground internal and external taper.
- With Balluffchip bore.
- Shanks hard turned (for smooth running).
- HSK mating faces machined.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Machining strategy: HSC

Overhang dimension A: 160 mm

External Ø D: 48 mm

Technical description

Overhang dimension A	160 mm
Morse taper internal	4
External Ø D	48 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm

Concentricity	≤ 8 μm
Machining strategy	HSC
Type of product	Arbor adapter