



## Top jaws set, 3 pieces, for chuck type: 160



### Order data

Order number	313450 160
GTIN	4019208193441
Item class	33R

### Description

#### Version:

**Precision milled** slots and serrations, **burnished**.

Bevelled for small clamping  $\emptyset$ .

#### Material:

Quality product made of 16MnCr5.

#### Suitable for:

**Heavy-duty chucks** from Schunk, RöhM and other heavy-duty chuck manufacturers.

#### Optional extras:

T-nuts No. 313505 – 313605.

#### Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

Bore spacing b	22 mm
for thread DIN 912	M12
Slot width D	17 mm
Hole centre spacing a	15 mm
Length L	78 mm
Height H	40 mm

for chuck type	160 mm
Width B	35 mm
Type of product	Heavy-duty lathe chuck jaws