



MT reducing adapter for locking threads, HSK-A 100, MT internal: 2



Order data

Order number	306790 2
GTIN	4045197505149
Item class	31A

Description

Version:

- Precision ground internal and external taper.
- With Balluffchip bore.
- Shanks hard turned (for smooth running).
- HSK mating faces machined.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Arbor standard: DIN 69893

Arbor standard: ISO 12164-1

Shape: A

Balance quality G at rotational speed: G 6.3 at 8,000 rpm

Concentricity: $\leq 8 \mu\text{m}$

Machining strategy: HSC

Overhang dimension A: 120 mm

External \varnothing D: 32 mm

Technical description

Morse taper internal	2
Overhang dimension A	120 mm
External \varnothing D	32 mm
Adapter	HSK-A 100
Arbor standard	DIN 69893

Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 8 μm
Machining strategy	HSC