



Top jaws set, 3 pieces, for chuck type: 200



Order data

Order number	313450 200
GTIN	4019208193458
Item class	33R

Description

Version:

Precision milled slots and serrations, **burnished**.

Bevelled for small clamping \emptyset .

Material:

Quality product made of 16MnCr5.

Suitable for:

Heavy-duty chucks from Schunk, Röhmm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

Length L	98 mm
Width B	35 mm
for chuck type	200 mm
Height H	40 mm
Hole centre spacing a	15 mm
Bore spacing b	22 mm

Slot width D	17 mm
for thread DIN 912	M12
Type of product	Heavy-duty lathe chuck jaws