

**Top jaws set, 3 pieces, for chuck type: 254****Order data**

Order number	313700 254
GTIN	4019208193687
Item class	33R

**Description****Version:**

**Precision milled** slots and serration, **burnished**.

**Material:**

Quality product made of 16MnCr5.

**Suitable for:**

**Heavy-duty chucks** from Schunk, Röhmm and other heavy-duty chuck manufacturers.

**Optional extras:**

T-nuts No. 313505 – 313605.

**Note:**

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

**Technical description**

Height H	45 mm
Hole centre spacing a	30 mm
Bore spacing b	30 mm
for chuck type	254 mm
Slot width D	16 mm
Length L	110 mm
Width B	50 mm

for thread DIN 912	M12
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws