

Garant
MT reducing adapter with tang, HSK-A 100, MT internal: 2

Order data

Order number	306970 2
GTIN	4045197290564
Item class	31A

Description
Version:

- **Precision ground internal and external taper.**
- **With Balluffchip bore.**
- **Shanks hard turned (for smooth running).**
- **HSK mating faces machined.**

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Machining strategy: HSC

Overhang dimension A: 120 mm

External \varnothing D: 32 mm

Technical description

Morse taper internal	2
Overhang dimension A	120 mm
External \varnothing D	32 mm
Adapter	HSK-A 100
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 8 μm
Machining strategy	HSC
Type of product	Arbor adapter