

**Garant**
**MT reducing adapter with tang, HSK-A 100, MT internal: 1**

**Order data**

Order number	306970 1
GTIN	4045197290557
Item class	31A

**Description**
**Version:**

- **Precision ground internal and external taper.**
- **With Balluffchip bore.**
- **Shanks hard turned (for smooth running).**
- **HSK mating faces machined.**

**Optional extras:**

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Machining strategy: HSC

Overhang dimension A: 110 mm

External  $\varnothing$  D: 25 mm

**Technical description**

Overhang dimension A	110 mm
Morse taper internal	1
External $\varnothing$ D	25 mm
Adapter	HSK-A 100
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 8 μm
Machining strategy	HSC
Type of product	Arbor adapter