

**Garant**
**MT reducing adapter with tang, HSK-A 100, MT internal: 3**

**Order data**

Order number	306970 3
GTIN	4045197290571
Item class	31A

**Description**
**Version:**

- **Precision ground internal and external taper.**
- **With Balluffchip bore.**
- **Shanks hard turned (for smooth running).**
- **HSK mating faces machined.**

**Optional extras:**

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Machining strategy: HSC

Overhang dimension A: 150 mm

External  $\varnothing$  D: 40 mm

**Technical description**

Morse taper internal	3
Overhang dimension A	150 mm
External $\varnothing$ D	40 mm
Adapter	HSK-A 100
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 8 μm
Machining strategy	HSC
Type of product	Arbor adapter