

Garant
Boring bar blank, HSK-F 63, A dimension: 200 mm

Order data

Order number	307022 200
GTIN	4045197587954
Item class	31A

Description
Version:

- **Taper and collar hardened and ground.**
- **Shank soft for further machining.**

Application:

For making special tools.

Material:

16MnCr5.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Shape: F

External Ø D: 63 mm

Technical description

Overhang dimension A	200 mm
External Ø D	63 mm
Adapter	HSK-F 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	F
Type of product	Boring bar blank

Accessories

HSK coolant tube for HSK 63

309880 63