

**ER clamping nut, for ER: 40****Order data**

Order number	309580 40
GTIN	4045197151971
Item class	32Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity. **With slots.**

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrench, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

Overall length L	26 mm
for ER	40 mm
Thread	M50×1.5
maximum tightening torque	240 Nm

External Ø D	63 mm
Standard	DIN 6499 D
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Type of product	Clamping nut

Accessories

ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40
ER chuck key for ER collet chuck 40	309680 40