



ER clamping nut for sealing rings, for ER: 16



Order data

| | |
|--------------|---------------|
| Order number | 309615 16 |
| GTIN | 7640128492160 |
| Item class | 39Z |

Description

Version:

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With hexagon 25 AF.**

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrench, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Sealing rings No. 309625; 309630; 309635; 309645.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

| | |
|---------------------------|---------|
| Overall length L | 22.5 mm |
| Thread | M22×1.5 |
| maximum tightening torque | 80 Nm |

| | |
|---------------------------------------|---------------------|
| for ER | 16 mm |
| External Ø D | 28 mm |
| Standard | DIN 6499 D |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Type of product | Clamping nut |