



## ER clamping nut for sealing rings, for ER: 32



### Order data

Order number	309615 32
GTIN	7640128492191
Item class	39Z

### Description

**Version:**

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With slots.**

**Suitable for:**

All standard ER collet chucks.

**Optional extras:**

ER clamping wrench, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Sealing rings No. 309625; 309630; 309635; 309645.

**Note:**

Collet chuck and clamping nut are balanced separately!

### Technical description

maximum tightening torque	180 Nm
for ER	32 mm
Overall length L	27.5 mm

Thread	M40×1.5
External Ø D	50 mm
Standard	DIN 6499 D
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Type of product	Clamping nut