

**Garant****ER clamping nut High Speed, for ER: 40****Order data**

Order number	309610 40
GTIN	4045197292100
Item class	31Z

**Description****Version:**

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With slots.**

**Suitable for:**

All standard ER collet chucks.

**Optional extras:**

ER clamping wrench, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

**Note:**

Collet chuck and clamping nut are balanced separately!

**Technical description**

for ER	40 mm
Thread	M50×1.5
Overall length L	26 mm

maximum tightening torque	240 Nm
External Ø D	63 mm
Standard	DIN 6499 D
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Type of product	Clamping nut

---

## Accessories

ER chuck key 1/2 inch socket for ER collet chuck 40	309700 40
ER chuck key for ER collet chuck 40	309680 40