



## Clamping head smooth, SK 65, Clamping $\varnothing$ (0.5 mm increments): 15mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 329930 15     |
| GTIN         | 2050001072580 |
| Item class   | 33H           |

### Description

#### Version:

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

#### Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

#### Note:

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

### Technical description

|                        |        |
|------------------------|--------|
| Clamping $\varnothing$ | 15 mm  |
| Profile                | round  |
| Clamping face          | smooth |
| Hardness               | 60 HR  |
| Length L               | 53 mm  |

|                 |                    |
|-----------------|--------------------|
| Version         | shortened fittings |
| Adapter         | SK 65              |
| Type of product | Clamping head      |