



Top jaw set, 3 pieces, soft, for chuck type: 100mm



Order data

Order number	314400 100
GTIN	4019208034539
Item class	33R

Description

Version:

Precision milled contact face, **not burnished.**

Application:

For fitting to hardened base jaws.

Material:

16 MnCr5

Suitable for:

Three-jaw lathe chucks No. 310505; 310655; 310705.

Note:

- **Jaws can generally be renewed in the chuck as long as the guide in the body is not worn out.**
- **Top, turning, and drilling jaws bought subsequently must be ground in the chuck for radial and axial run-out.**

Technical description

Bore spacing b	24 mm
for chuck type	100 mm
Slot width D	7.96 mm
Length L	53 mm
Height H	30 mm
Tenon length A	9.49 mm

suitable for colour code	Röhм geared scroll chucks and jaws
Type of product	Gear scroll chuck jaws