



Top jaw set, 4 pieces, soft, for chuck type: 100 mm



Order data

Order number	314500 100
GTIN	4019208034591
Item class	36R

Description

Version:

Precision milled contact face, **not burnished**.

Application:

For fitting to hardened base jaws.

Material:

16 MnCr5

Suitable for :

Four-jaw lathe chucks No. 312000; 312500; 312700.

Note:

- **Jaws can generally be renewed in the chuck as long as the guide in the body is not worn out.**
- **Top, turning, and drilling jaws bought subsequently must be ground in the chuck for radial and axial run-out.**

Aluminium top jaws **on request**.

suitable for colour code: Röhm geared scroll chucks and jaws

Length L: 53 mm

Height H: 30 mm

Slot width D: 7.96 mm

Bore spacing b: 24 mm

Tenon length A: 9.49 mm

Technical description

Slot width D	7.96 mm
Bore spacing b	24 mm

Height H	30 mm
for chuck type	100 mm
Tenon length A	9.49 mm
Length L	53 mm
suitable for colour code	Röhm geared scroll chucks and jaws
Type of product	Gear scroll chuck jaws