

**Clamping head smooth, SK 65, Clamping  $\varnothing$  (0.5 mm increments): 65mm****Order data**

Order number	329930 65
GTIN	2050001075994
Item class	33H

**Description****Version:**

Smooth version for precision machining.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

**Application:**

Versatile application range: machining centres, measuring machines, and pallet clamping.

**Note:**

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

**Technical description**

Clamping $\varnothing$	65 mm
Hardness	60 HR
Clamping face	smooth
Profile	round
Length L	53 mm

Version	shortened fittings
Adapter	SK 65
Type of product	Clamping head