



## Hydraulic chuck short, slim, HSK-A 63, Clamping range $\varnothing$ D1: 8mm



### Order data

Order number	307508 8
GTIN	2050001653284
Item class	33W

### Description

#### Version:

- Axial length adjustment, adjustment travel 10 mm.
- With RFID/Balluffchip bore.

#### Application:

- High metal removal rate (but not for extreme heavy machining).
- For drilling, reaming, and milling.

#### Optional extras:

Reducing sleeves No. 302135 – 302187, coolant tube No. 309880, socket wrench No. 309890, parallel wipers No. 343720.

WTE stop screws for direct clamping and for use of reducing sleeves on request.

#### Note:

A-dimension = 200 mm available on request!

### Technical description

$\varnothing$ D <sub>2</sub>	28 mm
L <sub>2</sub>	25 mm
Thread M	M6
Clamping $\varnothing$ D <sub>1</sub>	8 mm
L <sub>3</sub>	24 mm
Overhang dimension A	70 mm

External Ø D	50 mm
Adjustment travel V	10 mm
Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Shape	A
Through-coolant	yes, with max. 80 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

---

## Accessories

Cylindrical cleanerPlastic Pin Ø 8 mm	343720 8
---------------------------------------	----------