

Garant**ER Mini clamping nut, for ER: 11****Order data**

Order number	309650 11
GTIN	4045197292117
Item class	31Z

Description**Version:**

Small external dimensions, case-hardened and ground on all faces.

· **Case-hardened and ground on all faces.**

Suitable for:

ER collet chuck Mini No. 300650; 300652; 300665; 300685; 305710; 305712; 305715; 300649; 300651; 300661; 300684; 300667; 300669; 305707; 305709; 305717; 305721; 305723.

Technical description

Thread	M13×0.75
for ER	11 mm
maximum tightening torque	25 Nm
Overall length L	12 mm
External Ø D	16 mm
Standard	DIN 6499
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Machining strategy	HSC

Type of product

Clamping nut