

**FAHRION®**  
PRAZISION
**CP sealing ring, DI25, Clamping Ø (1 mm increments): 10 mm**

**Order data**

Order number	309667 10
GTIN	2050001705129
Item class	34F

**Description**
**Version:**

Vulcanised sealing rings up to 80 bar.  
 0.5 mm collet Ø clamping range (+ 0.4 / – 0.1).

**Suitable for :**

ER CP clamping nuts No. 309665 size 25DI.

**Note:**

**Not compatible with other sealing ring systems!**

**FAHRION system** ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

- **Sealing rings in 0.5 mm increments on request.**
- **Sealing rings for No. 309665 DI40 on request.**

External Ø D: 20.2 mm

Height L: 2 mm

**Technical description**

Clamping Ø	10 mm
Series	Centro P
for type	DI25
External Ø D	20.2 mm

Height L

---

2 mm