



ER clamping nut CENTRO P for HP sealing rings, Type CP for ER: 40DI



Order data

Order number	309665 40DI
GTIN	2050001736710
Item class	34F

Description

Version:

Mini = all sizes with "M", extremely slim design.

MiniSlim = sizes with "MS", extremely super slim design.

Conical = all sizes with "C".

Standard = all other sizes.

With trapezoidal thread for high clamping forces. Extra long double guidance of the ER clamping nut. ER clamping nuts coated for reduction of **friction**.

ER clamping nut CP, **for HP sealing rings**.

Note:

FAHRION system ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

Only the nominal size can be clamped (no intermediate range!)

Clamping range: 3 - 26 mm

Overall length L: 34.8 mm

External Ø D: 63 mm

maximum tightening torque: 200 N·m

Thread: Tr50×1.5

Technical description

maximum tightening torque	200 N·m
Overall length L	34.8 mm
Clamping range	3 - 26 mm
External Ø D	63 mm
Series	Centro P
Thread	Tr50×1.5
Type of product	Clamping nut