

**Garant****ER Mini clamping nut, for ER: 20****Order data**

|              |               |
|--------------|---------------|
| Order number | 309650 20     |
| GTIN         | 4045197292131 |
| Item class   | 31Z           |

**Description****Version:**

Small external dimensions, case-hardened and ground on all faces.

· **Case-hardened and ground on all faces.**

**Suitable for:**

**ER collet chuck Mini** No. 300650; 300652; 300665; 300685; 305710; 305712; 305715; 300649; 300651; 300661; 300684; 300667; 300669; 305707; 305709; 305717; 305721; 305723.

**Technical description**

|                                       |                     |
|---------------------------------------|---------------------|
| Thread                                | M24×1               |
| maximum tightening torque             | 40 Nm               |
| Overall length L                      | 19.5 mm             |
| for ER                                | 20 mm               |
| External Ø D                          | 28 mm               |
| Standard                              | DIN 6499            |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Machining strategy                    | HSC                 |

Type of product

Clamping nut