



High performance cutting oil foam, chlorine-free, Contents: 0,4l



Order data

Order number	084225 0,4
GTIN	2050001660800
Item class	08J

Description

Version:

Cutting oil for the most demanding applications. Recommended for mixing with normal mineral-based cutting oil (but not with water-soluble oils).

Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

Application:

Multi-purpose for **all machining operations** (turning, milling, drilling, tapping, reaming, broaching and sawing) and also for **forming**. Indispensable when cutting **difficult materials** such as stainless and heat-resistant steels, nickel alloys, titanium, and similar alloys. Ideal for **non-ferrous metals**.

Strongly clinging cutting oil foam for spot application to the cutting zone. Contains no sulphur or mineral oils, can be precisely applied, and washed off with water.

Technical description

Labelling of hazardous substances	GHS02: Flame
Labelling of hazardous substances	GHS07 caution

Version	Spray can
Solubility in water	soluble
Boiling point	-24 °C
Spontaneous ignition temperature	235 °C
Spray head	Smart Straw
Colour	pale yellow
Storage temperature	15 - 35 °C
Contents	0.4 l
Type of product	Cutting oil / grinding oil