

FAHRION®
PRAZISION
CP sealing ring, DI25, Clamping Ø (1 mm increments): 12 mm

Order data

| | |
|--------------|---------------|
| Order number | 309667 12 |
| GTIN | 2050001705143 |
| Item class | 34F |

Description
Version:

Vulcanised sealing rings up to 80 bar.
 0.5 mm collet Ø clamping range (+ 0.4 / – 0.1).

Suitable for :

ER CP clamping nuts No. 309665 size 25DI.

Note:

Not compatible with other sealing ring systems!

FAHRION system ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

- **Sealing rings in 0.5 mm increments on request.**
- **Sealing rings for No. 309665 DI40 on request.**

External Ø D: 20.2 mm

Height L: 2 mm

Technical description

| | |
|--------------|----------|
| Clamping Ø | 12 mm |
| Series | Centro P |
| for type | DI25 |
| External Ø D | 20.2 mm |

Height L

2 mm