

**Garant****ER Mini clamping nut for sealing rings, for ER: 16****Order data**

Order number	309652 16
GTIN	4045197645715
Item class	31Z

**Description****Version:**

Small external dimensions, case-hardened and ground on all faces.

· **Case-hardened and ground on all faces.**

**Suitable for :**

**ER collet chuck Mini** No. 300650; 300652; 300665; 300685; 305710; 305712; 305715; 300649; 300651; 300661; 300684; 300667; 300669; 305707; 305709; 305717; 305721; 305723.

Machining strategy: HSC

Overall length L: 22.5 mm

External Ø D: 22 mm

Thread: M19×1

maximum tightening torque: 35 N·m

**Technical description**

Overall length L	22.5 mm
maximum tightening torque	35 N·m
Thread	M19×1
for ER	16 mm
External Ø D	22 mm

Standard	DIN 6499
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Machining strategy	HSC
Type of product	Clamping nut