

HAINBUCH
**Clamping head with transverse and longitudinal serrations, SK 65, Clamping
 Ø (0.5 mm increments): 29,5mm**


Order data

Order number	329934 29,5
GTIN	2050001076205
Item class	33H

Description

Version:

With transverse and longitudinal serrations for raw material.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping Ø	29.5 mm
Hardness	60 HR
Profile	round
Clamping face	Transverse and longitudinal serrations

Length L	58 mm
Adapter	SK 65
Type of product	Clamping head