

**Garant****ER Mini clamping nut for sealing rings, for ER: 20****Order data**

Order number	309652 20
GTIN	4045197645722
Item class	31Z

**Description****Version:**

Small external dimensions, case-hardened and ground on all faces.

· **Case-hardened and ground on all faces.**

**Suitable for :**

**ER collet chuck Mini** No. 300650; 300652; 300665; 300685; 305710; 305712; 305715; 300649; 300651; 300661; 300684; 300667; 300669; 305707; 305709; 305717; 305721; 305723.

Machining strategy: HSC

Overall length L: 24 mm

External Ø D: 28 mm

Thread: M24×1

maximum tightening torque: 40 N·m

**Technical description**

maximum tightening torque	40 N·m
for ER	20 mm
Thread	M24×1
Overall length L	24 mm
External Ø D	28 mm

Standard	DIN 6499
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Machining strategy	HSC
Type of product	Clamping nut