

FAHRION®
FAHREYOND FREESHOW
ER clamping nut CENTRO P for HP sealing rings, Type CP for ER: 16CDI

Order data

Order number	309665 16CDI
GTIN	2050001704900
Item class	34F

Description
Version:

Mini = all sizes with "M", extremely slim design.

MiniSlim = sizes with "MS", extremely super slim design.

Conical = all sizes with "C".

Standard = all other sizes.

With trapezoidal thread for high clamping forces. Extra long double guidance of the ER clamping nut. ER clamping nuts coated for reduction of **friction**.

ER clamping nut CP, **for HP sealing rings**.

Note:

FAHRION system ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

Only the nominal size can be clamped (no intermediate range!)

Clamping range: 1 - 10 mm

Overall length L: 26.2 mm

External Ø D: 24 mm

maximum tightening torque: 55 N·m

Thread: Tr21×1.5

Technical description

Clamping range	1 - 10 mm
Overall length L	26.2 mm
maximum tightening torque	55 N·m
External Ø D	24 mm
Series	Centro P
Thread	Tr21×1.5
Type of product	Clamping nut

Accessories

CP roller bearing wrench Type 16C	309754 16C
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 3 mm	309666 3
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 10 mm	309666 10
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 7 mm	309666 7
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 1 mm	309666 1
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 2 mm	309666 2
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 9 mm	309666 9
CP roller bearing wrench for torque wrenches Type 16C	309756 16C
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 6 mm	309666 6
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 8 mm	309666 8
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 5 mm	309666 5
Sealing ring HP for ER clamping nut CENTRO P Clamping Ø (1 mm increments) 4 mm	309666 4

